

**Garant****Circular saw blade, trapezoidal flat teeth INOX, Blade Ø D: 355mm****Order data**

Order number	584004 355
GTIN	4045197883735
Item class	51S

**Description****Version:**

**Tipped with carbide inserts**, precision version with high-strength blade, noise damped. Generously dimensioned carbide teeth allow multiple re-grinding.

**Application:**

**Universal saw blade** for machining **stainless steel** with crosscut and mitre saws. Problem-free cutting off of pipes, sheet metal, profiles and solid material. Suitable for both steel and non-ferrous materials. Not suitable for cast iron. Low-burr, quick cutting without cooling.

**Technical description**

Blade Ø D	355 mm
Bore Ø	25.4 mm
Number of teeth	84
Width of cut B	2.4 mm
Tooth version	Trapezoidal flat teeth
Type of product	Circular saw blade

