

Garant**Circular saw blade, trapezoidal flat teeth Steel, Blade Ø D: 305mm****Order data**

Order number	584008 305
GTIN	4045197883742
Item class	51S

Description**Version:**

Tipped with carbide inserts, precision version with high-strength blade, noise damped. Generously dimensioned carbide teeth allow multiple re-grinding.

Application:

For cutting **stainless steel** with crosscut and mitre saws. Problem-free cutting of mild steel profiles, pipes and plates. Low-burr, quick cutting without cooling.

Technical description

Width of cut B	2.2 mm
Blade Ø D	305 mm
Tooth version	Trapezoidal flat teeth
Number of teeth	60
Bore Ø	25.4 mm
Type of product	Circular saw blade

