



Bi-hexagon socket, 1/4 inch, Width across flats: 7mm



Order data

Order number	630950 7
GTIN	4018754000326
Item class	63A

Description

Version:

Forged from high quality steel, internally bevelled for easy fitting to bolt heads.

Square drive socket with hole to DIN 3120 D 6.3.

Optimum grain orientation due to special forging process. Close tolerance width across flats.

No rounding of bolt corners, nuts and bolt heads are protected. Hardened in an oil bath, stress-relieved and distortion-free for a precision fit. Rounded surface with **AS Drive** profile.

Standard:

DIN 3124

Material:

HPQ® high performance steel, non-flaking chrome-plated over nickel.

Note:

PLEASE NOTE!

An alternative from GARANT is also available for this product.

Recommended product number: 630929

Technical description

Width across flats	7 mm
Ø drive output end	10.7 mm
Length	23 mm
Square drive	1/4 in

Drive profile	Bi-hex socket
Type of product	Socket insert