

## Plug gauge "Go" chrome H7, Nominal size Ø: 56mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 484040 56     |
| GTIN         | 2050001955487 |
| Item class   | 48B           |

### Description

#### Version:

The "Go" ends of these working gauges have a **wear allowance** to DIN 7164.

**"Go" end with hard chrome measuring faces.** This increases the gauge life about 8 times.

#### Standard:

Toleranz und Abmaße nach **DIN EN ISO 1938-1, DIN 2245-1 und DIN 7164.**

#### Note:

- **Further intermediate sizes available on request or can simply be ordered at [www.hoffmann-group.com](http://www.hoffmann-group.com), for instance No. 484000 size 82.**

### Technical description

|                 |                 |
|-----------------|-----------------|
| Tolerance zone  | H               |
| Standard        | DIN 7150-2      |
| Standard        | DIN 7164        |
| Quality         | 7               |
| Nominal size    | 56 mm           |
| Type of gauge   | "Go" plug gauge |
| Type of gauge   | "No Go" gauge   |
| Calibration     | M2              |
| Type of product | Pug Gauge       |

### Services

DAkKS calibration "Go" / "No Go" plug gauge maximum  $\varnothing$   
60 mm

028340 60

Calibration "Go" / "No Go" plug gauge maximum  $\varnothing$  60 mm

028300 60