



Installation pliers with opening spring VDE insulated, Overall length: 200mm



Order data

Order number	728788 200
GTIN	4003773075110
Item class	73F

Description

Version:

Multi-function pliers for electrical installation work, with screwed joint for precise "no play" action.

- **Gripping flat and round material.**
- **Bending wires and copper conductors.**
- **Deburring and widening flush-mounted boxes.**
- **Cutting copper cables up to \varnothing 15 mm (5×2.5 mm²).**
- **Stripping copper wires 0.75 to 1.5 mm² and 2.5 mm².**
- **Crimping terminal sleeves 0.5 to 2.5 mm².**

Handles with grips **insulated to DIN EN IEC 60900 / VDE 0682-201**.

With opening spring.

Material:

Special tool steel, jaws chrome-plated, handles with multi-component covering.

Technical description

Cutting capacity	5×2.5 mm ²
Wire stripping for conductor \varnothing	2.5 mm ²
Wire stripping for conductor \varnothing	0.7 – 1.5 mm ²
for terminal sleeves	0.5 – 2.5 mm ²
overall length	200 mm
Weight	280 g

Cutting capacity up to Ø	15 mm
Joint	screwed
with return spring	yes
Handle	Multi-component covering
Standard	DIN EN IEC 60900 / VDE 0682-201
Material	Special tool steel
Surface	chrome-plated
Type of product	Multi-function pliers