



Electronics side cutter Super Knips[®], kW, overall length: 140mm



Order data

| | |
|--------------|---------------|
| Order number | 726480 140 |
| GTIN | 4003773081647 |
| Item class | 73F |

Description

Version:

Slim head with precision ground cutting edges, with fine cutting chamfer. Handles with multi-component covering, with opening spring.

Standard:

DIN ISO 9654

Material:

Made of stainless steel (INOX).

Technical description

| | |
|---|---|
| overall length | 140 mm |
| Cutter length | 12.3 mm |
| Head width | 15.7 mm |
| Cutting capacity copper wire up to Ø | 0.2 - 2.1 mm |
| Cutting capacity medium-hard steel wire | 0.2 - 1.2 mm |
| Cutting chamfer | without bevel |
| Material | Stainless steel, INOX |
| Standard | DIN ISO 9654 |
| Handle | Multi-component covering |
| Manufacturing process | Cutting edges induction hardened (approx. 54 HRC) |

| | |
|------------------------|----------------|
| Product name attribute | kW |
| with return spring | yes |
| with wire holder | no |
| Type of product | Cutting pliers |