

Dräger**Full-face mask X-plore® 6300, Size: UNI****Order data**

Order number	097249 UNI
GTIN	4026056002405
Item class	09I

Description**Version:**

The high-performance, **single-filter full-face** mask stands for proven **quality and reliability** for protection of the respiratory system and the eyes. The tough, EPDM-based mask body with its double sealed frame and three-fold sealing lines ensures **reliable and comfortable seating** on virtually all shapes of face. This distortion-free and scratch-resistant visor of PMMA (Perspex) guarantees a **large field of view** with wide all-round vision. An **intelligent ventilation system** with separate inner mask ensures a condensation-free visor. The 5-point-strap attachment allows the mask to be put on smoothly, without complications and without catching on the hair. With standard round thread connection RD40 to EN 148-1.

Standard:

EN 136 Klasse 2

Technical description

Manufacturer's designation	R 55 800
Product features	Silicone-free
Lens coating	free of condensation

Lens coating	scratch-resistant
Weight	500 g
Filter connection	RD40
Lens material	PMMA
Colour code for suitable accessories	RD40
Type of product	Full-face mask body

Accessories

Visor protection film, self-adhesive, pack of 25 Type FOIL	097269 FOIL
Replacement visor for Dräger full-face masks Lens material PMMA	097268 PMMA
Exchangeable filter Filter AX	097264 AX
Exchangeable filter Filter A2B2E2K1	097264 A2B2E2K1
Interchangeable particle filter Filter P3	097262 P3
Exchangeable filter Filter A2P3RD	097264 A2P3RD
Carrying box for respirator Type BAG1	097267 BAG1
Anti-fogging agent for viewing visor Type CLEAN	097266 CLEAN
Exchangeable filter Filter A2B2P3RD	097264 A2B2P3RD
Glasses frame Type FRAME	097265 FRAME