



LED true colour cordless work lamp, Type: MULTI2

Order data

Order number	081514 MULTI2
GTIN	5708997354476
Item class	08C

Description

Version:

COLOUR MATCH. Special LED with high CRI value for **perfect colour reproduction** and extremely long LED working life. Perfect for all painting, polishing, cleaning and preparation work. Designed for use in paint shops. **Exchangeable glass lens** and resistant to all types of solvent, even when cleaned every day. With a **2 COLOUR LIGHT function**. This allows the choice between two colour temperatures depending on the work in hand. Warm light (4500 K) for light surfaces and cold light (6500 K) for dark surfaces.

MULTIMATCH 2. Powerful portable cordless work light with 5-step dimmer function. Display at the back, showing the battery capacity and remaining working time. Integral adjustment base for direct mounting on **Scangrip stand 081252 1.35-3**.

Supplied with:

Charging cable, 11.1 V / 4400mAh Li-ion battery.

IP Index of Protection: IP 67

Illumination: 2500 lm

Working life: 14 h

Light colour CRI: 96

Lamp body length: 235 mm

Lamp body width: 233 mm

Weight: 2.1 g

Technical description

Type of product