

**Turning tool right-hand, similar to DIN 4971 (ISO 1), M20, Shank square: 12mm****Order data**

Order number	296030 12
GTIN	4045197884657
Item class	22E

Description**Version:**

Fitted with diamond ground carbide inserts.

Application:

P20/K25 for machining steel and cast iron.

M20 for machining stainless steels.

Attention:

For rough and interrupted machining the cutting edges should be sharpened with a boron carbide hand lapper (No. 558812).

Technical description

Shank square	12 mm
Overall length	100 mm
Tool material	M20
Type of product	Turning tool