



Turning tool right-hand, similar to DIN 4971 (ISO 1), M20, Shank square: 25mm



Order data

Order number	296030 25
GTIN	4045197884688
Item class	22E

Description

Version:

Fitted with diamond ground carbide inserts.

Application:

P20/K25 for machining steel and cast iron.

M20 for machining stainless steels.

Attention:

For rough and interrupted machining the cutting edges should be sharpened with a boron carbide hand lapper (No. 558812).

Technical description

Shank square	25 mm
Overall length	140 mm
Tool material	M20
Type of product	Turning tool