

HOLEX

Turning tool left-hand, similar to DIN 4972 (ISO 2), P20/K25, Shank square: 10mm



Order data

Order number	296225 10
GTIN	4045197884701
Item class	22E

Description

Version:

Fitted with diamond ground carbide inserts.

Application:

P20/K25 for machining steel and cast iron.

M20 for machining stainless steels.

Attention:

For rough and interrupted machining the cutting edges should be sharpened with a boron carbide hand lapper (No. 558812).

Technical description

Shank square	10 mm
Overall length	100 mm
Tool material	P20/K25
Type of product	Turning tool