



Turning tool right-hand, similar to DIN 4972 (ISO 2), M20, Shank square: 12mm



Order data

| | |
|--------------|---------------|
| Order number | 296130 12 |
| GTIN | 4045197884725 |
| Item class | 22E |

Description

Version:

Fitted with diamond ground carbide inserts.

Application:

P20/K25 for machining steel and cast iron.

M20 for machining stainless steels.

Attention:

For rough and interrupted machining the cutting edges should be sharpened with a boron carbide hand lapper (No. 558812).

Technical description

| | |
|-----------------|--------------|
| Shank square | 12 mm |
| Overall length | 100 mm |
| Tool material | M20 |
| Type of product | Turning tool |