



## Internal turning tool right-hand, similar to DIN 4973 (ISO 8), M20, Shank square: 10mm



### Order data

Order number	296330 10
GTIN	4045197884770
Item class	22E

### Description

**Version:**

Fitted with diamond ground carbide inserts.

**Application:**

P20/K25 for machining steel and cast iron.

M20 for machining stainless steels.

**Attention:**

For rough and interrupted machining the cutting edges should be sharpened with a boron carbide hand lapper (No. 558812).

### Technical description

Shank square	10 mm
for bores from $\varnothing$	18 mm
Overall length	150 mm
Tool material	M20
Type of product	Turning tool