



Internal turning tool right-hand, similar to DIN 4973 (ISO 8), M20, Shank square: 16mm



Order data

Order number	296330 16
GTIN	4045197884794
Item class	22E

Description

Version:

Fitted with diamond ground carbide inserts.

Application:

P20/K25 for machining steel and cast iron.

M20 for machining stainless steels.

Attention:

For rough and interrupted machining the cutting edges should be sharpened with a boron carbide hand lapper (No. 558812).

Technical description

for bores from \varnothing	27 mm
Shank square	16 mm
Overall length	210 mm
Tool material	M20
Type of product	Turning tool