

FLUKE®

Non-contact voltage testers



Order data

Order number	473005
GTIN	095969290814
Item class	47H

Description

Version:

Compact voltage tester for non-contact detection of live conductors.

Function:

IP40: Protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away, and offers no protection against water.

Application:

Testing of cables, sockets, junction boxes etc., if voltage is present, the measuring prod lights up red and sounds a beep signal.

IP Index of Protection: IP 40

Display range AC: 200 - 1000 V

Overvoltage category: CAT IV / 1000 V

Article no of the battery / rechargeable battery fitted: 081561 LR3

Technical description

Display range AC	200 - 1000 V
IP Index of Protection	IP 40
Overvoltage category	CAT IV / 1000 V
Number of batteries contained	2
Article no of the battery / rechargeable battery fitted	081561 LR3
Power supply	Battery-powered
Type of product	Non-contact voltage tester

Services

Calibration Voltage tester	017870
----------------------------	--------

Accessories

Alkaline-manganese batteries International size LR3	081556 LR3
Alkaline-manganese batteries International size LR3	081561 LR3