

FLUKE.

Multimeter, Type: 175**Order data**

Order number	473322 175
GTIN	095969095921
Item class	47H

Description**Version:**

Ergonomic plastic housing with integral holster. Large LCD display for good legibility. Reliable and easy to use – **warning if the test leads are connected wrongly**. The leading measuring tools for troubleshooting electrical and electronic systems for professional technicians. Robust, reliable and precise.

Application:

Digital service multimeters for a wide range of applications, very high safety and other additional functions.

Standard:

IEC 61010; ANSI/ISA S82.02.01; CSA C22.2-1010.1

Supplied with:

Battery 081561 6LR61, test leads, and removable insulating caps.

Technical description

Overvoltage category	CAT III 1000 V
Overvoltage category	CAT IV 600 V
AC current	0.1 mA – 10 A

Information displayed	6000
Capacitance	1 nF – 10 mF
DC current	0.1 mA – 10 A
Measurement process	TRUE RMS
Resistance	0.1 Ω – 50 M Ω
Calibration	I3
Basic accuracy	0.15 %
Frequency	0.01 Hz – 100 kHz
AC voltage	0.1 mV – 1000 V
DC voltage	0.1 mV – 1000 V
Diode testing	yes
Display backlit	no
Continuity testing	yes
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081561 6LR61
Power supply	Battery-powered
Type of product	Multimeter

Services

DAkkS calibration Digital multimeter Number of decimal places 3	027010 3
Calibration Digital multimeter Number of decimal places 3	027000 3

Accessories

Test leads Measuring tips \varnothing 1 mm	473318 1
Carrying case C150 Type F	473337 F
Magnetic meter hanger Type TPAK	473329 TPAK
Test leads Measuring tips \varnothing 2 mm	473318 2