

FLUKE.

**Voltage and continuity tester, Type: T130****Order data**

Order number	473090 T130
GTIN	095969610506
Item class	47H

**Description****Version:**

Two-pole voltage testers with ergonomic one-handed operation for sockets. Measured value display with backlighting. Battery indicator - if the battery is flat the measured voltage can continue to be displayed. Slip-on test prods with wear display. **VDE version**

**Function:**

IP64: Protected against splashed water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

**Application:**

For professional multi-stage voltage, polarity and continuity testing.

**Standard:**

**HSE GS 38 (Messspitzen); IEC EN 61243-3.**

**Technical description**

FI/RCD protective switch test current	yes
Display	LED / LCD
Display range AC	6 - 690 V

Display range DC	6 - 690 V
Phase testing	100V – 690V
Calibration	I1
Illumination of probe points	yes
Three phase sequence testing	yes
Polarity testing	yes
Continuity testing	visual / acoustic
Overvoltage category	CAT III 690 V
Overvoltage category	CAT IV 600 V
IP Index of Protection	IP 64
Frequency measurement	40 - 400 Hz
Torch function	yes
Number of batteries contained	2
Article no of the battery / rechargeable battery fitted	081551 LR3
Power supply	Battery-powered
Type of product	Voltage tester

## Services

CalibrationVoltage tester Type S	027120 S
DAkkS calibrationVoltage tester Type S	027160 S

## Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
---	------------