

FLUKE.

Voltage and continuity tester, Type: T90**Order data**

Order number	473090 T90
GTIN	095969599672
Item class	47H

Description**Version:**

Two-pole voltage testers with ergonomic one-handed operation for sockets. Measured value display with backlighting. Battery indicator - if the battery is flat the measured voltage can continue to be displayed. Slip-on test prods with wear display.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Application:

For professional multi-stage voltage, polarity and continuity testing.

Standard:

HSE GS 38 (Messspitzen); IEC EN 61243-3.

Technical description

Frequency measurement	40 - 400 Hz
FI/RCD protective switch test current	yes
Continuity testing	visual / acoustic

Display range AC	12 - 690 V
Calibration	I1
IP Index of Protection	IP 54
Overvoltage category	CAT III 600 V
Overvoltage category	CAT II 690 V
Display range DC	12 - 690 V
Polarity testing	yes
Display	LED
Torch function	yes
Number of batteries contained	2
Article no of the battery / rechargeable battery fitted	081551 LR3
Power supply	Battery-powered
Type of product	Voltage tester

Services

CalibrationVoltage tester Type S	027120 S
DAkkS calibrationVoltage tester Type S	027160 S

Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
---	------------