

FLUKE.

Clamp meter, Type: 323**Order data**

Order number	473290 323
GTIN	095969623742
Item class	47H

Description**Version:**

Current clamps with large easy-to-read LCD display in a slim and ergonomic design. True effective value measurements and optimised ergonomics for troubleshooting in industrial and building technology applications.

Standard:

EN 61010-1

Supplied with:

Incl. test leads and padded carrying case. Batteries 2 pcs. No. 081561 size LR3.

Technical description

Resistance	0.1 Ω – 4000 Ω
Information displayed	4000
DC voltage	0.1 V – 600 V
AC voltage	0.1 V – 600 V
Memory function	HOLD

Overvoltage category	CAT III 600 V
Overvoltage category	CAT IV 300 V
maximum jaw aperture	30 mm
Measurement process	TRUE RMS (AC)
AC current	0.1 A - 400 A
Basic accuracy	2 %
Number of batteries contained	2
Article no of the battery / rechargeable battery fitted	081561 LR3
Power supply	Battery-powered
Power supply	2× 081561 LR3
Standard	EN 61010-1
Calibration	I4
Type of product	Current clamp

Services

CalibrationClamp meter Type D	027050 D
DAkkS calibrationClamp meter Type D	027060 D

Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
---	------------