



## Corner turning tool right-hand, similar to DIN 4978 (ISO 3), P20/K25, Shank square: 10mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 296745 10     |
| GTIN         | 4045197884480 |
| Item class   | 22E           |

### Description

**Version:**

Fitted with diamond ground carbide inserts.

**Application:**

P20/K25 for machining steel and cast iron.

M20 for machining stainless steels.

**Attention:**

For rough and interrupted machining the cutting edges should be sharpened with a boron carbide hand lapper (No. 558812).

### Technical description

|                 |              |
|-----------------|--------------|
| Shank square    | 10 mm        |
| Overall length  | 90 mm        |
| Tool material   | P20/K25      |
| Type of product | Turning tool |