

**Corner turning tool right-hand, similar to DIN 4978 (ISO 3), P20/K25, Shank square: 16mm****Order data**

Order number	296745 16
GTIN	4045197885401
Item class	22E

**Description****Version:**

Fitted with diamond ground carbide inserts.

**Application:**

P20/K25 for machining steel and cast iron.

M20 for machining stainless steels.

**Attention:**

For rough and interrupted machining the cutting edges should be sharpened with a boron carbide hand lapper (No. 558812).

**Technical description**

Shank square	16 mm
Overall length	110 mm
Tool material	P20/K25
Type of product	Turning tool