

HOLEX**Grooving tool right-hand, similar to DIN 4981 (ISO 7), M20, Shank height: 20mm****Order data**

Order number	297030 20
GTIN	4045197885555
Item class	22E

Description**Version:**

Fitted with diamond ground carbide inserts.

Application:

P20/K25 for machining steel and cast iron.

M20 for machining stainless steels.

Attention:

For rough and interrupted machining the cutting edges should be sharpened with a boron carbide hand lapper (No. 558812).

Overall length: 125 mm

Shank width: 12 mm

Blade width: 5 mm

Technical description

Shank height	20 mm
Blade width	5 mm
Shank width	12 mm
Overall length	125 mm
Tool material	M20
Type of product	Turning tool

