

HOLEX**Grooving tool right-hand, similar to DIN 4981 (ISO 7), M20, Shank height: 20mm**

Order data

Order number	297030 20
GTIN	4045197885555
Item class	22E

Description

Version:

Fitted with diamond ground carbide inserts.

Application:

P20/K25 for machining steel and cast iron.

M20 for machining stainless steels.

Attention:

For rough and interrupted machining the cutting edges should be sharpened with a boron carbide hand lapper (No. 558812).

Technical description

Shank height h	20 mm
Blade width	5 mm
Overall length	125 mm
Shank width b	12 mm
Tool material	M20
Type of product	Turning tool