



## Bi-hexagon socket, 1/4 inch, Width across flats: 11 mm



### Order data

Order number	630950 11
GTIN	4018754000364
Item class	63A

### Description

#### Version:

Forged from high quality steel, internally bevelled for easy fitting to bolt heads.

Square drive socket with hole to DIN 3120 D 6.3.

Optimum grain orientation due to special forging process. Close tolerance width across flats.

No rounding of bolt corners, nuts and bolt heads are protected. Hardened in an oil bath, stress-relieved and distortion-free for a precision fit. Rounded surface with **AS Drive** profile.

#### Standard:

**DIN 3124**

#### Material:

HPQ® high performance steel, non-flaking chrome-plated over nickel.

#### Note:

**PLEASE NOTE!**

An alternative from GARANT is also available for this product.

Recommended product number: 630929

### Technical description

Ø drive output end	15.5 mm
Length	23 mm
Width across flats	11 mm
Square drive	1/4 in

Drive profile	Bi-hex socket
Type of product	Socket insert