

**HOLEX****Grooving tool right-hand, similar to DIN 4981 (ISO 7), M20, Shank height: 25mm**

## Order data

Order number	297030 25
GTIN	4045197885562
Item class	22E

## Description

**Version:**

Fitted with diamond ground carbide inserts.

**Application:**

P20/K25 for machining steel and cast iron.

M20 for machining stainless steels.

**Attention:**

For rough and interrupted machining the cutting edges should be sharpened with a boron carbide hand lapper (No. 558812).

## Technical description

Blade width	6 mm
Shank height h	25 mm
Overall length	140 mm
Shank width b	16 mm
Tool material	M20
Type of product	Turning tool