

Garant**Table trolley with height-adjustable platform TA9, Type: TA92****Order data**

Order number	918557 TA92
GTIN	4045197885319
Item class	91T

Description**Version:**

Welded steel construction, platform of chipboard with anthracite-coloured scratch-resistant surface. **Height is adjustable manually** by means of a hand crank. By this means the platform can be moved up and down with **4 mechanical spindle lifting pillars**. Handle of impact-resistant polypropylene with a Haptoprene® insert, this can be swung up in order to operate the hand crank. 2 fixed wheels and 2 castors (with parking brake) with treadless polyurethane tyres and roller bearings.

Colour:

Silver and anthracite **powder-coated**.

Note:

For reasons of safety no perforated panel can be fitted.

Height adjustment range: 680 - 970 mm

Width: 1040 mm

Depth: 509 mm

Platform area width: 890 mm

Platform area depth: 500 mm

Height of bottom shelf: 195 mm

Technical description

Depth	509 mm
Platform area width	890 mm
Weight	67.6 kg
Height adjustment range	680 - 970 mm
Height of bottom shelf	195 mm
Load capacity of top shelf	200 kg
Wheel Ø	125 mm
Type	TA92
maximum load capacity	250 kg
Width	1040 mm
Platform area depth	500 mm
Type of product	Table trolleys