

bimos

Swivel work chair, PU foam, with castors, low, Colour: BLACK**Order data**

Order number	965301 BLACK
GTIN	4016849624464
Item class	96B

Description**Version:**

Seat and backrest of soft PU foam. Easy-care, washable, robust and resistant to weak acids and alkalis as well as to mechanical impacts.

Ergonomic comfort padding with lumbar support and handy push handles.

Standard:**DIN 68877**

Load capacity chair: 120 kg

Height adjustment range: 450 - 630 mm

Seat width: 460 mm

Seat depth: 470 mm

Backrest height: 580 mm

Colour of seat material: black

Technical description

Material of base	Steel
Seat depth	470 mm

stepless height adjustment	yes
Support frame version	5-point star base
Backrest height	580 mm
Material of backrest	PU foam
Weight	14 kg
Base version	Set of castors
Colour of seat material	black
Type of height adjustment	Height adjustment lever
Height adjustment version	Gas pressure spring
Material of seat surface	PU foam
Armrest pair can be adjusted	yes
Seat width	460 mm
Series	Work-Tec
Version	with castors
Load capacity chair	120 kg
Height adjustment range	450 - 630 mm
Type of product	Swivel work chair

Accessories

Castors (1 set = 5 pieces)	963187
----------------------------	--------