



LED head lamp, Manufacturer's designation: H8R



Order data

Order number	081486 H8R
GTIN	4058205005623
Item class	04B

Description

Version:

Powerful high-quality LED headlamps **Very strong illumination (600 Lumen)** and compact. **One-hand focussing** and exchangeable and rechargeable USB battery box. Backlight and charge status display.

IP Index of Protection: IP 54

Manufacturer's designation: H8R

ATEX zone: no

Illumination: 10 - 600 lm

Working life: 10 - 120 h

Number of rechargeable batteries contained: 1

Type of rechargeable battery: Lithium-ion

Technical description

Manufacturer's designation	H8R
IP Index of Protection	IP 54
Illumination	10 - 600 lm
Head Ø	36 mm
Smart Light Technology (SLT)	yes
Advanced Focus System (AFS)	yes
Rapid Focus	yes

Battery voltage	3.6 V
Illumination range	20 - 150 m
ATEX zone	no
Including belt pocket	no
Power supply	12
Weight	158 g
Working life	10 - 120 h
Battery capacity	3.2 A·h
Number of rechargeable batteries contained	1
Type of rechargeable battery	Lithium-ion
Dimmable lighting	no