

KERN**Compact scales type ECB, maximum weighing range: 10000g****Order data**

Order number	479452 10000
GTIN	4045761161429
Item class	47D

Description**Version:**

Large background illuminated LCD display (character height 21 mm). Weighing plate made of stainless steel.

Very simple operation with 2 keys.

- **Tare function (cumulative weighing function) for easy zeroing of the display.**
- **Battery-powered, auto-off after 3 minutes.**
- **Can be powered using a mains adaptor.**

Optional extras:

6 batteries No. 081561 size LR6; mains adaptor or rechargeable battery on request.

Technical description

Height	60 mm
Depth	300 mm
Dimensions of weighing plate	320×260
Scale divisions	5 g
Width	320 mm
Net weight	2.6 kg
maximum weighing range	10000 g
Number of batteries contained	2

Article no of the battery / rechargeable battery fitted	081561 LR6
Power supply	Battery-powered
Calibration	K2
Type of product	Compact balance

Services

CalibrationScales maximum weighing range 50 kg	027700 50
DAkkS calibrationScales maximum weighing range 50	027710 50

Accessories

Alkaline-manganese batteries International size LR6	081561 LR6
---	------------