

KERN**Platform scales, type EOB, maximum weighing range: 150Lkg**

Order data

Order number	479600 150L
GTIN	4045761124738
Item class	47D

Description

Version:

- **Robust parcel scales for the dispatch department.**
- **Very simple operation with four buttons.**
- **Display unit with numeral height 25 mm can be placed away from the platform; can be positioned or mounted using the flexible cable approx. 2 m long.**
- **Suitable for mains and battery operation, auto-off after 3minutes.**

Supplied with:

Mains adapter and wall bracket for display unit.

Optional extras:

6 batteries No. 081561 size LR6, stand for the display unit available on request.

Technical description

Reproducibility	50 g
Display unit height	50 mm
Display unit depth	110 mm
Dimensions of weighing plate	550×550 mm
Net weight	11 kg

Display unit width	215 mm
Scale divisions	50 g
Calibration	Price on request
Power supply	Battery-powered
Number of batteries contained	6
Article no of the battery / rechargeable battery fitted	081561 LR6
Number height display unit	25 mm
Type of product	Platform balance

Services

CalibrationScales maximum weighing range 150 kg	027700 150
DAkkS calibrationScales maximum weighing range 180	027710 180

Accessories

Alkaline-manganese batteries International size LR6	081561 LR6
---	------------