



Small double open ended spanner set, chrome-plated over nickel, Number of keys: 13



Order data

Order number	612400 13
GTIN	4018754080519
Item class	63A

Description

Version:

With very slim heads. Unequal jaw angles (15° and 75°), same jaw width each end.

Application:

Especially for fitting work in the most restricted places.

Material:

Chrome alloy steel; non-flaking, chrome-plated over nickel.

Supplied with:

1 each small double open ended spanner No. 612200 / 612205: Size 4; 4.5; 5; 5.5; 6; 7; 8; 9; 10; 11; 12; 13; 14

Technical description

Number of keys	13
Width across flats	metric
Jaw position 1	15 degrees
Jaw position 2	75 degrees
Material	Chrome alloy steel
Surface	chrome-plated over nickel
Type of product	Spanner

Accessories

Small double open ended spanner Width across flats 13 mm	612200 13
Small double open ended spanner Width across flats 6 mm	612200 6
Small double open ended spanner Width across flats 10 mm	612200 10
Small double open ended spanner Width across flats 5,5 mm	612200 5,5
Small double open ended spanner Width across flats 7 mm	612200 7
Small double open ended spanner Width across flats 8 mm	612200 8
Small double open ended spanner Width across flats 11 mm	612200 11
Small double open ended spanner Width across flats 12 mm	612200 12
Small double open ended spanner Width across flats 4,5 mm	612200 4,5
Small double open ended spanner Width across flats 9 mm	612200 9
Small double open ended spanner Width across flats 14 mm	612200 14
Small double open ended spanner Width across flats 4 mm	612200 4
Small double open ended spanner Width across flats 5 mm	612200 5