

**Fleece finishing belt (A) DF-BL, 13×305 mm, Grit equivalent: 180****Order data**

Order number	558476 180
GTIN	4054596624306
Item class	53M

**Description****Version:**

Tear-resistant and flexible fleece finishing belt with high **edge stability**.

Flexible fleece belt for use on hand-held machines.

Synthetic nylon non-woven fabric with synthetic resin bonded abrasive grit, long service life, **consistent surface finish, low heat generation**.

**Application:**

For deburring, matting and finishing. The **low-stretch fabric backing** is particularly suitable for heavier loadings on pneumatic grinding machines.

**Technical description**

Grit designation	medium
Grit equivalent	180
Version	A medium
Colour	red
Series	DF-BL

Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
Linishing belt width	13 mm
Linishing belt length	305 mm
Product name attribute	13×305 mm
Type of product	Fleece linishing belt

### User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable	20-25 m/s	
Steel < 900 N/mm <sup>2</sup>	suitable	20 m/s	P
Steel < 1400 N/mm <sup>2</sup>	suitable	20 m/s	P
Steel < 55 HRC	suitable	20 m/s	H
Steel < 60 HRC	suitable	20 m/s	H
Steel < 67 HRC	suitable	20 m/s	H
INOX	suitable	20 m/s	
Ti	suitable	20 m/s	
GG(G)	suitable	20 m/s	K
CuZn	suitable	20 m/s	N
Plastic, GRP	suitable	20 m/s	
Wood	suitable	20 m/s	
Paint	suitable	20 m/s	
Uni	suitable	20 m/s	
dry	suitable		