



## Tool24 PickOne – master system DE, Total number of compartments: 320

### Order data

Order number	979200 320
GTIN	4045197886019
Item class	9SA

### Description

#### Version:

Goods issuing system with innovative drum system to ensure secure individual withdrawal of every item. Very quick goods removal due to low access times, self-opening compartment and visual signal at the correct withdrawal compartment. The drum of the Tool24 PickOne is available with up to 4 different compartment sizes as standard configuration and with a load capacity of more than 1000 kg, specially designed for industrial use. Flexible attachment of a touch screen thanks to double-sided perforated panel.

The master system can be extended with additional slave systems and combined with all the Tool24 hardware variants. 2 compartment variants, ideal for discharging of item portfolios with similar dimensions, such as gloves.

#### Supplied with:

Touch screen 22 inches, barcode scanner, PC including Basic software package.

#### Colour:

Fronts light grey RAL 7035, body signal blue RAL 5005 **powder-coated**.

#### Note:

The drum of the Tool24 PickOne is individually and uniquely configurable for each customer with 4 different storage sizes depending on the portfolio of items to be issued. Talk to your technical adviser.

The weights do not include a PC and monitor.

Cabinet housing internal load capacity: 1000 kg

Hoffmann perforated panel grid interval: 9×9 mm

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Height: 2000 mm

Width: 1080 mm

Depth: 875 mm

Number of compartments B: 160

Number of compartments C: 160

Weight: 275 kg

### Technical description

Cabinet housing internal load capacity	1000 kg
Hoffmann perforated panel grid interval	9×9 mm
Drawer runner extension	
Material thickness	mm
Drawer runner extension (partial/full extension)	%
Door opening angle	degrees
Height adjustment interval	mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Cylinder lock	
Safety certificate	
Type of product	