



Precision ratchet "Zyklop Speed" reversible, 3/8 inch with swivel head and ejector



Order data

Order number	635190
GTIN	4013288121875
Item class	63F

Description

Version:

Ratchet head can be swivelled with defined engagement positions at 0° (use like a screwdriver) and 75° and 90° positions to either side. Working arc 5°, with ejector and reversing plate for right-hand and left-hand threads.

Standard:

Außenvierkante nach **DIN 3120-A 10** mit federnder Kugel, für Innenvierkante nach **DIN 3120-C 10** mit Rillen.

Material:

Chrome vanadium steel, chrome-plated.

Suitable for :

Manual use.

Square drive: 3/8 in

No. of teeth: 72

Technical description

Manufacturer's designation	8000 B
Square drive	3/8 in
overall length	199 mm
No. of teeth	72
Working angle	5°
Material	Chrome vanadium steel
Surface	chrome-plated

Type of product

Ratchet