



## Precision ratchet "Zyklop Speed" reversible, 3/8 inch with swivel head and ejector



### Order data

Order number	635190
GTIN	4013288121875
Item class	63F

### Description

#### Version:

**Ratchet head can be swivelled** with defined engagement positions at 0° (use like a screwdriver) and 75° and 90° positions to either side. Working arc 5°, with ejector and reversing plate for right-hand and left-hand threads.

#### Standard:

Außenvierkant nach **DIN 3120-A 10** mit federnder Kugel, für Innenvierkant nach **DIN 3120-C 10** mit Rillen.

#### Material:

Chrome vanadium steel, chrome-plated.

#### Suitable for:

Manual use.

### Technical description

Manufacturer's designation	8000 B
Square drive	3/8 in
overall length	199 mm
No. of teeth	72
Working angle	5 degrees
Material	Chrome vanadium steel
Surface	chrome-plated
Type of product	Ratchet

