



Double open ended spanner set, Number of keys: 8



Order data

Order number	611000 8
GTIN	4018754057535
Item class	63A

Description

Version:

Drop-forged. With close tolerance jaw widths.

With easy-grip fluted shaft. Optimum flex resistance, good torque transmission.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome alloy steel, non-flaking chrome-plated over nickel; smoothed finish.

Supplied with:

1 each double open ended spanner No. 610600 / 610100 / 610900 / 610950 / 610120: Size 6×7; 8×9; 10×11; 12×13; 14×15; 16×17; 18×21; 19×22

Technical description

Number of keys	8
Width across flats	metric
Jaw position 1	15 degrees
Jaw position 2	15 degrees
Type of product	Spanner

Accessories

Double open ended spanner Jaw widths 12X13 mm	610100 12X13
Double open ended spanner Jaw widths 6X7 mm	610100 6X7
Double open ended spanner Jaw widths 10X11 mm	610100 10X11
Double open ended spanner Jaw widths 19X22 mm	610100 19X22
Double open ended spanner Jaw widths 8X9 mm	610100 8X9
Double open ended spanner Jaw widths 14X15 mm	610100 14X15
Plastic clip holder for number of sockets 8	611500 8
Double open ended spanner Jaw widths 18X21 mm	610100 18X21
Double open ended spanner Jaw widths 16X17 mm	610100 16X17