



Small double open ended spanner, Width across flats: 10mm



Order data

| | |
|--------------|---------------|
| Order number | 612200 10 |
| GTIN | 4018754018611 |
| Item class | 63A |

Description

Version:

With very slim heads. Unequal jaw angles (15° and 75°), same jaw width each end.

Application:

Especially for fitting work in the most restricted places.

Material:

Chrome alloy steel; non-flaking, chrome-plated over nickel.

Technical description

| | |
|----------------------|---------------------------------------|
| Width across flats 1 | 10 mm |
| maximum jaw height h | 3 mm |
| maximum jaw width b1 | 21 mm |
| Width across flats | metric |
| Spanner length L | 105 mm |
| Jaw position 1 | 15 degrees |
| Jaw position 2 | 75 degrees |
| Material | Chrome alloy steel |
| Surface | non-flaking chrome-plated over nickel |
| Type of product | Spanner |

