



Double open ended spanner set, Number of keys: 10



Order data

Order number	611000 10
GTIN	4018754057542
Item class	63A

Description

Version:

Drop-forged. With close tolerance jaw widths.

With easy-grip fluted shaft. Optimum flex resistance, good torque transmission.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome alloy steel, non-flaking chrome-plated over nickel; smoothed finish.

Supplied with:

1 each double open ended spanner No. 610600 / 610100 / 610900 / 610950 / 610120: Size 6×7; 8×9; 10×11; 12×13; 14×15; 16×17; 18×19; 20×22; 21×24; 27×30

Technical description

Number of keys	10
Width across flats	metric
Jaw position 1	15 °
Jaw position 2	15 °
Type of product	Spanner

Accessories

Plastic clip holder with closure flap for number of sockets 11	611700 11
Double open ended spanner Jaw widths 8X9 mm	610100 8X9
Double open ended spanner Jaw widths 20X22 mm	610100 20X22
Double open ended spanner Jaw widths 14X15 mm	610100 14X15
Double open ended spanner Jaw widths 16X17 mm	610100 16X17
Double open ended spanner Jaw widths 21X24 mm	610100 21X24
Double open ended spanner Jaw widths 12X13 mm	610100 12X13
Double open ended spanner Jaw widths 18X19 mm	610100 18X19
Double open ended spanner Jaw widths 10X11 mm	610100 10X11
Double open ended spanner Jaw widths 27X30 mm	610100 27X30
Double open ended spanner Jaw widths 6X7 mm	610100 6X7