

**Crowfoot spanner, Width across flats: 14mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 612800 14     |
| GTIN         | 4024089009897 |
| Item class   | 66A           |

**Description****Version:**

Drop forged, robust shank and powerful jaw.

**Application:**

For use where access is difficult.

**Material:**

Chrome vanadium steel, chrome-plated.

**Note:**

For suitable tommy bars see No. 621600 – 621800.

**Technical description**

|                       |                       |
|-----------------------|-----------------------|
| Width across flats    | 14 mm                 |
| Bore Ø                | 8.5 mm                |
| Spanner length, L     | 160 mm                |
| Head thickness h      | 5.5 mm                |
| Manufacturing process | drop forged           |
| Material              | Chrome vanadium steel |
| Surface               | chrome-plated         |
| Type of product       | Spanner               |

**Accessories**

|                                                               |              |
|---------------------------------------------------------------|--------------|
| Tommy bar, cylindrical $\varnothing$ ×overall length 8X180 mm | 621600 8X180 |
| Tommy bar, stepped overall length 175 mm                      | 621800 175   |
| Tommy bar, stepped overall length 245 mm                      | 621800 245   |
| Tommy bar, stepped overall length 180 mm                      | 621800 180   |