

**Small double open ended spanner, Width across flats: 11 mm****Order data**

Order number	612200 11
GTIN	4018754018628
Item class	63A

Description**Version:**

With very slim heads. Unequal jaw angles (15° and 75°), same jaw width each end.

Application:

Especially for fitting work in the most restricted places.

Material:

Chrome alloy steel; non-flaking, chrome-plated over nickel.

Technical description

maximum jaw width b1	24.2 mm
Width across flats 1	11 mm
maximum jaw height h	3 mm
Width across flats	metric
Spanner length L	116 mm
Jaw position 1	15 degrees
Jaw position 2	75 degrees
Material	Chrome alloy steel
Surface	non-flaking chrome-plated over nickel
Type of product	Spanner

