



Double open ended spanner set, Number of keys: 12



Order data

Order number	611000 12
GTIN	4018754057559
Item class	63A

Description

Version:

Drop-forged. With close tolerance jaw widths.

With easy-grip fluted shaft. Optimum flex resistance, good torque transmission.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome alloy steel, non-flaking chrome-plated over nickel; smoothed finish.

Supplied with:

1 each double open ended spanner No. 610600 / 610100 / 610900 / 610950 / 610120: Size 6×7; 8×9; 10×11; 12×13; 14×15; 16×17; 18×19; 20×22; 21×23; 24×26; 27×32; 30×34

Note:

PLEASE NOTE!

An alternative from GARANT is also available for this product.

Recommended product number: 610610

Technical description

Number of keys	12
Width across flats	metric
Jaw position 1	15 degrees
Jaw position 2	15 degrees
Type of product	Spanner

Accessories

Double open ended spanner Jaw widths 6X7 mm	610100 6X7
Double open ended spanner Jaw widths 27X32 mm	610100 27X32
Double open ended spanner Jaw widths 12X13 mm	610100 12X13
Double open ended spanner Jaw widths 24X26 mm	610100 24X26
Double open ended spanner Jaw widths 18X19 mm	610100 18X19
Plastic clip holder for number of sockets 12	611500 12
Double open ended spanner Jaw widths 21X23 mm	610100 21X23
Double open ended spanner Jaw widths 10X11 mm	610100 10X11
Double open ended spanner Jaw widths 20X22 mm	610100 20X22
Double open ended spanner Jaw widths 30X34 mm	610100 30X34
Double open ended spanner Jaw widths 8X9 mm	610100 8X9
Double open ended spanner Jaw widths 14X15 mm	610100 14X15
Double open ended spanner Jaw widths 16X17 mm	610100 16X17