



## Small double open ended spanner, Width across flats: 5mm



### Order data

Order number	612200 5
GTIN	4018754018567
Item class	63A

### Description

**Version:**

With very slim heads. Unequal jaw angles (15° and 75°), same jaw width each end.

**Application:**

Especially for fitting work in the most restricted places.

**Material:**

Chrome alloy steel; non-flaking, chrome-plated over nickel.

### Technical description

maximum jaw width b1	12.6 mm
maximum jaw height h	2 mm
Width across flats 1	5 mm
Width across flats	metric
Spanner length L	78 mm
Jaw position 1	15 degrees
Jaw position 2	75 degrees
Material	Chrome alloy steel
Surface	non-flaking chrome-plated over nickel
Type of product	Spanner

