



Double open ended spanner set, Number of keys: 7ZOLL



Order data

Order number	611000 7ZOLL
GTIN	4018754080762
Item class	63A

Description

Version:

Drop-forged. With close tolerance jaw widths.

With easy-grip fluted shaft. Optimum flex resistance, good torque transmission.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome alloy steel, non-flaking chrome-plated over nickel; smoothed finish.

Supplied with:

1 each double open ended spanner No. 610600 / 610100 / 610900 / 610950 / 610120: 1/4×5/16; 3/8×7/16; 1/2×9/16; 5/8×3/4; 11/16×13/16; 7/8×15/16; 1.1/8×1.5/16 inch in a textile tool roll

Technical description

Number of keys	7
Width across flats	imperial
Jaw position 1	15 degrees
Jaw position 2	15 degrees
Type of product	Spanner

Accessories

Double open ended spanner, inch Type 3	610120 3
Double open ended spanner, inch Type 13	610120 13
Double open ended spanner, inch Type 8	610120 8
Double open ended spanner, inch Type 1	610120 1
Double open ended spanner, inch Type 22	610120 22
Plastic clip holder for number of sockets 8	611500 8
Double open ended spanner, inch Type 32	610120 32
Double open ended spanner, inch Type 16	610120 16
Double open ended spanner, inch Type 5	610120 5