



Double open ended spanner set, Number of keys: 11ZOLL



Order data

Order number	611000 11ZOLL
GTIN	4018754080779
Item class	63A

Description

Version:

Drop-forged. With close tolerance jaw widths.

With easy-grip fluted shaft. Optimum flex resistance, good torque transmission.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome alloy steel, non-flaking chrome-plated over nickel; smoothed finish.

Supplied with:

1 each double open ended spanner No. 610600 / 610100 / 610900 / 610950 / 610120: 1/4×5/16; 3/8×7/16; 1/2×9/16; 9/16×5/8; 19/32×11/16; 5/8×3/4; 11/16×13/16; 3/4×7/8; 25/32×13/16; 7/8×15/16; 1.1/8×1.5/16 inch in a textile tool roll

Technical description

Number of keys	11
Width across flats	imperial
Jaw position 1	15 degrees
Jaw position 2	15 degrees
Type of product	Spanner

Accessories

Double open ended spanner, inch Type 19	610120 19
Double open ended spanner, inch Type 8	610120 8
Double open ended spanner, inch Type 22	610120 22
Double open ended spanner, inch Type 32	610120 32
Double open ended spanner, inch Type 1	610120 1
Double open ended spanner, inch Type 3	610120 3
Plastic clip holder for number of sockets 12	611500 12
Double open ended spanner, inch Type 13	610120 13
Double open ended spanner, inch Type 9	610120 9
Double open ended spanner, inch Type 10	610120 10
Double open ended spanner, inch Type 16	610120 16
Double open ended spanner, inch Type 18	610120 18
Double open ended spanner, inch Type 5	610120 5