

**Crowfoot wrench Jaw design, Width across flats: 14mm****Order data**

| | |
|--------------|---------------|
| Order number | 612900 14 |
| GTIN | 4018754003518 |
| Item class | 63A |

Description**Version:**

Drop forged, head with square socket for drive tools such as ratchet, extension etc.

Application:

The possibility of accepting various different drive tools means that access to restricted places is made easier.

Material:

Chrome alloy steel, chrome-plated, round finish surface (no sharp edges).

Note:

For suitable drive tools see No. 632000 – 641350 and 655230 – 657766.

Technical description

| | |
|--------------------|--------------------|
| Square drive | 3/8 in |
| Width across flats | 14 mm |
| Head thickness h | 6.3 mm |
| Head width b | 30 mm |
| Length L | 37.7 mm |
| Form, output drive | Jaw design |
| Material | Chrome alloy steel |

| | |
|-----------------|---------------|
| Surface | chrome-plated |
| Type of product | Socket insert |

Accessories

| | |
|--|------------|
| Extension, 3/8 inch overall length 40 mm | 635400 40 |
| Extension, 3/8 inch flexible overall length 194 mm | 635600 194 |
| Extension, 3/8 inch overall length 160 mm | 635400 160 |
| Flexi-head ratchet, 3/8 inch with ejector | 635335 |
| Special extension 3/8 inch | 612950 |
| Extension, 3/8 inch overall length 240 mm | 635400 240 |
| T-handle, 3/8 inch overall length 200 mm | 635729 200 |
| Extension, 3/8 inch extra long overall length 711 mm | 635500 711 |
| Extension, 3/8 inch QuickRelease overall length 240 mm | 635645 240 |
| Universal joint, 3/8 inch Type 3/8 | 636220 3/8 |
| Extension, 3/8 inch overall length 75 mm | 635400 75 |
| Extension, 3/8 inch overall length 240 mm | 635429 240 |
| Universal joint, 3/8 inch Type 3/8 | 636229 3/8 |
| Precision ratchet "Zyklop Speed" reversible, 3/8 inch with swivel head and ejector | 635190 |
| Extension, 3/8 inch QuickRelease overall length 75 mm | 635645 75 |
| Extension, 3/8 inch overall length 75 mm | 635420 75 |
| Universal joint, 3/8 inch Type 3/8 | 636200 3/8 |
| T-handle, 3/8 inch QuickRelease overall length 165 mm | 635750 165 |
| T-handle, 3/8 inch overall length 165 mm | 635700 165 |
| Extension, 3/8 inch QuickRelease overall length 160 mm | 635645 160 |
| Extension, 3/8 inch overall length 125 mm | 635420 125 |
| Precision ratchet "Zyklop Metal" push-through square drive, 3/8 inch with ejector | 635290 |

| | |
|---|------------|
| Extension, 3/8 inch extra long overall length 305 mm | 635500 305 |
| Push-through ratchet, 3/8 inch with short handle | 635900 |
| Reversible precision ratchet 3/8 inch with ejector and twist handle | 635220 |
| Extension, 3/8 inch overall length 75 mm | 635429 75 |
| Precision ratchet "Zyklop Metal" reversible, 3/8 inch with ejector | 635295 |
| Swivel handle, 3/8 inch | 636000 |
| Extension, 3/8 inch overall length 125 mm | 635400 125 |
| T-handle, 3/8 inch overall length 200 mm | 635720 200 |
| Extension, 3/8 inch overall length 40 mm | 635420 40 |
| Universal joint, 3/8 inch QuickRelease Type 3/8 | 636250 3/8 |
| Extension, 3/8 inch extra long overall length 508 mm | 635500 508 |
| Reversible ratchet, 3/8 inch with ejector Type 3/8 | 635090 3/8 |
| Extension, 3/8 inch overall length 125 mm | 635429 125 |
| Reversible ratchet, 3/8 inch with ejector Type | 635025 |