



Small double open ended spanner set, chrome-plated over nickel, Number of keys: 7



Order data

Order number	612400 7
GTIN	4018754057757
Item class	63A

Description

Version:

With very slim heads. Unequal jaw angles (15° and 75°), same jaw width each end.

Application:

Especially for fitting work in the most restricted places.

Material:

Chrome alloy steel; non-flaking, chrome-plated over nickel.

Supplied with:

1 each small double open ended spanner No. 612200 / 612205: Size 4; 4.5; 5; 5.5; 6; 7; 8

Technical description

Number of keys	7
Width across flats	metric
Jaw position 1	15 degrees
Jaw position 2	75 degrees
Material	Chrome alloy steel

Surface	chrome-plated over nickel
Type of product	Spanner

Accessories

Small double open ended spanner Width across flats 4,5 mm	612200 4,5
Small double open ended spanner Width across flats 5,5 mm	612200 5,5
Small double open ended spanner Width across flats 6 mm	612200 6
Small double open ended spanner Width across flats 7 mm	612200 7
Small double open ended spanner Width across flats 4 mm	612200 4
Small double open ended spanner Width across flats 5 mm	612200 5
Small double open ended spanner Width across flats 8 mm	612200 8