

**Crowfoot wrench Jaw design, Width across flats: 17mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 612900 17     |
| GTIN         | 4018754003549 |
| Item class   | 63A           |

**Description****Version:**

Drop forged, head with square socket for drive tools such as ratchet, extension etc.

**Application:**

The possibility of accepting various different drive tools means that access to restricted places is made easier.

**Material:**

Chrome alloy steel, chrome-plated, round finish surface (no sharp edges).

**Note:**

For suitable drive tools see No. 632000 – 641350 and 655230 – 657766.

**Technical description**

|                    |                    |
|--------------------|--------------------|
| Width across flats | 17 mm              |
| Square drive       | 3/8 in             |
| Head thickness h   | 6.3 mm             |
| Head width b       | 38 mm              |
| Length L           | 42.5 mm            |
| Form, output drive | Jaw design         |
| Material           | Chrome alloy steel |

|                 |               |
|-----------------|---------------|
| Surface         | chrome-plated |
| Type of product | Socket insert |

## Accessories

|   |            |
|---|------------|
| T-handle, 3/8 inch overall length 165 mm  | 635700 165 |
| Extension, 3/8 inch overall length 75 mm  | 635429 75  |
| Reversible ratchet, 3/8 inch with ejector Type 3/8                                | 635090 3/8 |
| Extension, 3/8 inch overall length 240 mm   | 635429 240 |
| Universal joint, 3/8 inch Type 3/8  | 636220 3/8 |
| Reversible ratchet, 3/8 inch with ejector Type                                    | 635025     |
| Extension, 3/8 inch overall length 240 mm   | 635400 240 |
| Swivel handle, 3/8 inch   | 636000     |
| T-handle, 3/8 inch overall length 200 mm  | 635729 200 |
| Extension, 3/8 inch QuickRelease overall length 160 mm                            | 635645 160 |
| Push-through ratchet, 3/8 inch with short handle                                  | 635900     |
| Reversible precision ratchet 3/8 inch with ejector and twist handle               | 635220     |
| Universal joint, 3/8 inch Type 3/8  | 636200 3/8 |
| Precision ratchet "Zyklop Metal" reversible, 3/8 inch with ejector                | 635295     |
| Universal joint, 3/8 inch QuickRelease Type 3/8                                   | 636250 3/8 |
| Extension, 3/8 inch QuickRelease overall length 240 mm                            | 635645 240 |
| Extension, 3/8 inch overall length 160 mm   | 635400 160 |
| Precision ratchet "Zyklop Metal" push-through square drive, 3/8 inch with ejector | 635290     |
| Extension, 3/8 inch overall length 40 mm  | 635400 40  |
| Extension, 3/8 inch flexible overall length 194 mm                                | 635600 194 |
| T-handle, 3/8 inch QuickRelease overall length 165 mm                             | 635750 165 |
| Universal joint, 3/8 inch Type 3/8  | 636229 3/8 |

|  |            |
|--|------------|
| Extension, 3/8 inch QuickRelease overall length 75 mm                              | 635645 75  |
| Extension, 3/8 inch extra long overall length 305 mm                               | 635500 305 |
| Extension, 3/8 inch overall length 75 mm   | 635400 75  |
| Extension, 3/8 inch overall length 125 mm  | 635429 125 |
| Flexi-head ratchet, 3/8 inch with ejector  | 635335     |
| Extension, 3/8 inch overall length 75 mm   | 635420 75  |
| Special extension 3/8 inch   | 612950     |
| Extension, 3/8 inch extra long overall length 508 mm                               | 635500 508 |
| T-handle, 3/8 inch overall length 200 mm   | 635720 200 |
| Extension, 3/8 inch extra long overall length 711 mm                               | 635500 711 |
| Extension, 3/8 inch overall length 125 mm  | 635400 125 |
| Precision ratchet "Zyklop Speed" reversible, 3/8 inch with swivel head and ejector | 635190     |
| Extension, 3/8 inch overall length 40 mm   | 635420 40  |
| Extension, 3/8 inch overall length 125 mm  | 635420 125 |