




Velour-backed abrasive disc ABRANET®, Ø 150 mm, Grit: 80



Order data

Order number	567800 80
GTIN	6416868662948
Item class	56M

Description

Version:

Velour-backed abrasive discs consisting of a **mesh structure** of polyamide fabric containing thousands of holes and coated with abrasive grit.

Advantage:

- **Dust-free grinding: very low impact on workplace and environment.**
- **No clogging of the grinding wheel (surface defects and dust balls are avoided).**
- **Guaranteed improved surface finishes with less grinding media consumption.**
- **High effectiveness – the removal rate increases by several orders of magnitude depending on the surface.**

Application:

Grinding of paints, fillers primers, (fibre-reinforced) plastics, non-ferrous metals and aluminium alloys, furniture components.

Technical description

Grit	80
Disc Ø	150 mm
Series	ABRANET®
Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 150 mm

Propulsive equipment	Orbital sander
maximum circumferential speed	40 m/s
Type of product	Velour-backed abrasive disc

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable only under restricted conditions		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable		
dry	suitable		

Accessories

Multi-hole PU backing pad External Ø 147 mm	567990 147
PU hook and loop backing pad Multiple holes Outer Ø 150 mm	567887 150
PU hook and loop backing pad External Ø 150 mm	567885 150