

**Double open ended spanner DIN 895, Widths across flats: 6X7mm****Order data**

Order number	613000 6X7
GTIN	4045197384430
Item class	62A

Description**Version:**

Drop forged, jaw angle 15°, strong shaft.

Standard:

DIN 895

Material:

Special steel (strength 1200 – 1400 N/mm²).

Black oxidised finish.

Technical description

maximum jaw height h	3.5 mm
Width across flats 2	7 mm
Width across flats 1	6 mm
Width across flats	metric
Spanner length L	100 mm
Standard	DIN 895
Jaw position 1	15 degrees
Jaw position 2	15 degrees
Material	Special steel
Surface	burnished
Type of product	Spanner

