

**Double open ended spanner DIN 895, Widths across flats: 9X11 mm****Order data**

Order number	613000 9X11
GTIN	4045197384461
Item class	62A

**Description****Version:**

Drop forged, jaw angle 15°, strong shaft.

**Standard:**

**DIN 895**

**Material:**

Special steel (strength 1200 – 1400 N/mm<sup>2</sup>).

Black oxidised finish.

**Technical description**

maximum jaw height h	5 mm
Width across flats 1	9 mm
Width across flats 2	11 mm
Width across flats	metric
Spanner length L	125 mm
Standard	DIN 895
Jaw position 1	15 degrees
Jaw position 2	15 degrees
Material	Special steel
Surface	burnished
Type of product	Spanner

